

**Garant**
**Master Turn steel boring bar helical flutes A.. SVUBR, for indexable inserts VB., right-hand, Shank  $\varnothing$  / insert size: 16/11mm**

**Order data**

Order number	261128 16/11
GTIN	4062406711061
Item class	21T

**Technical description**

Centre offset $L_3$	11 mm
Pack of insert screws	269028 7
Setting angle $\kappa$	93 degrees
Head length $L_1$	31 mm
Overall length $L$	180 mm
suitable indexable insert	VB.. 1103..
ISO code toolholder	A16Q SVUBR/L11
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Shank $\varnothing D_s$	16 mm
Series	GARANT Master
Clamping height $L_2$	15 mm
Insert size	11 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar