

Garant
Master Turn steel boring bar helical flutes A.. SVUBL, for indexable inserts VB., left-hand, Shank \varnothing / insert size: 20/11mm

Order data

Order number	261129 20/11
GTIN	4062406711108
Item class	21T

Technical description

Overall length L	200 mm
Clamping height L ₂	18 mm
Series	GARANT Master
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	24 mm
ISO code toolholder	A20R SVUBR/L11
Setting angle κ	93 degrees
suitable indexable insert	VB.. 1103..
Shank $\varnothing D_s$	20 mm
Head length L ₁	36 mm
Centre offset L ₃	13 mm
Insert size	11 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar