

Garant

Master Eco clamping toolholder short PWLNR 95°, for indexable inserts WN., right-hand, Shank / insert size: 25/08mm



Order data

Order number	251910 25/08
GTIN	4062406734114
Item class	21U

Description

Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

suitable indexable insert	WN.. 0804..
Series	Master Eco
Insert size	8 mm
Shim	259031 48
Shank size	25 mm
Head length L ₁	30 mm
Spring	259046 4
ISO code toolholder	PWLNR/L 2525H08
Lever screw	259018 15

Functional width L ₄	32 mm
Overall length L	100 mm
Lever	259015 15
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	QuickTurn clamping toolholder