


Tubular socket wrench, angled, Width across flats: 10mm

Order data

Order number	621341 10
GTIN	4062406750619
Item class	62C

Description
Version:

Drop-forged for the most arduous duties with especially close-tolerance jaw widths. Special hollow form, even for nuts on long projecting threads. Same width across flats on both sides. Sizes 6 and 7 hexagon on both sides, from size 8 with hexagon on long arm and bi-hexagon on short arm. Angled at approx. 90 – 95°.

Material:

Chrome vanadium steel, chrome-plated.

Socket length L₁: 130 mm

Socket length L₂: 29 mm

Bore Ø F: 7 mm

Technical description

Socket length L ₂	29 mm
Drive profile	Hexagon socket
Drive profile	Bi-hex socket
Width across flats	10 mm
Drive profile short side	bi-hex
Drive profile long side	hexagon
Bore Ø F	7 mm
Socket length L ₁	130 mm

Angle	90 - 95 °
Material	Chromium vanadium steel
Surface	chrome-plated
both sides have the same width across flats	yes
Type of product	Socket spanner