



## Indexable drill holder Form E1, VDI 25, Bore d<sub>2</sub> (H6): 16mm



### Order data

Order number	319165 16
GTIN	4062406755188
Item class	32U

### Description

#### Application:

For drilling with indexable drill with internal coolant supply.

#### Standard:

DIN 69880 / VDI 3425, Blatt 2.

### Technical description

External Ø d <sub>3</sub>	36 mm
l <sub>1</sub> -0.2	67 mm
Bore d <sub>2</sub> (H6)	16 mm
l <sub>2</sub>	54 mm
Cooling channel thread	M8
Clamping screw thread	M10×1
Shape	E
VDI size	VDI 25
d <sub>6</sub>	58 mm
Colour code for VDI shanks	VDI 25

Type of product

VDI tool arbor