

**Face driver with Morse taper, Morse taper (MK): 4****Order data**

Order number	327400 4
GTIN	4062406764586
Item class	32P

Description**Version:**

- **Tip angle 60°, clamping Ø 17 mm – 54 mm.**
- **Clockwise and anti-clockwise rotation.**
- **Outstandingly suitable for use on lathes and when hobbing.**

Application:

For mounting in the headstock taper of the lathe.

Suitable for:

Lathe centres No. 321405, No. 321720, No. 321730 and 321740.

Supplied with:

Face driver with centring points 327410 and driver 327412.

Optional extras:

No. 327410 centring point, No. 327412 driver, No. 327414 damping elements.

Note:

Suitable taper sleeves for adapting in lathe chucks available on request.

Working range Ø: 19 - 34 mm

Clamping Ø D1: 17 mm

Reach B: 62 mm

Workpiece weight: 50 kg

External Ø: 42 mm

largest centre point Ø 60° A: 5 mm

Technical description

Workpiece weight	50 kg
------------------	-------

largest centre point Ø 60° A	5 mm
External Ø	42 mm
Reach B	62 mm
Clamping Ø D1	17 mm
Working range Ø	19 - 34 mm
Push-off screw	no
Type of product	Face driver