

**Burr set 8 pieces, Z steel – coarse, Carbide8****Order data**

Order number	547120 8
GTIN	4067263104582
Item class	52D

Description**Version:**

The innovative tooth geometry permits very high metal removal rates combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank \varnothing 6 mm.

Sets of burrs in the most popular shapes and sizes. Shank \varnothing 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Supplied with:

1 pc. each No. 540740 size A0616; A1020; A1225; C1225; D1009; G0820; F1225; L1020.

Technical description

Tooth type abbreviation	Z steel
Toothing grit designation	coarse
Series	Tooth configuration Z steel
Tool material	Carbide

Shank Ø	6 mm
Number of burrs	8
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		

Accessories

BurrZ steel – coarse Type A0616	540740 A0616
BurrZ steel – coarse Type A1020	540740 A1020
BurrZ steel – coarse Type A1225	540740 A1225
BurrZ steel – coarse Type C1225	540740 C1225
BurrZ steel – coarse Type D1009	540740 D1009
BurrZ steel – coarse Type F1225	540740 F1225
BurrZ steel – coarse Type G0820	540740 G0820
BurrZ steel – coarse Type L1020	540740 L1020