

Garant

**Shrink-fit chuck vibration-damped, with cooling channel bores, SK 50 A = 120,
Clamping range Ø D1: 6mm**

**Order data**

Order number	302214 6
GTIN	4062406787165
Item class	31A

Description**Version:**

- **High-temperature steel.**
- **Integrated length adjustment of the tools.**
- **For HSS and solid carbide tools.**
- **Shanks hard turned (smooth cutting action!).**
- **With RFID / Balluffchip bore.**
- **With coolant channel bores and threads that can be sealed.**
- **With tapped holes on each side for balancing screws.**
- **Reinforced version/contour.**
- **Polished surface.**
- **Specially mounted carbide core in the shrink-fit chuck body.**

Advantage:

- **Vibration-damping.**
- **Better workpiece surface finish.**
- **Optimised tool life.**
- **Increased process reliability.**
- **Lower corrosion tendency due to polished surface.**

Application:

For clamping tools with plain shank (h6 shank tolerance). Suitable for inductive, contact and hot air shrink-fit units.

Optional extras:

Pull studs (PS) No. 308600 – 308800.

PS wrenches No. 308820 – 308835.

Shrink-fit chuck extensions No. 302410 – 302419.

Shrink-fit units, accessories No. 354210 – 354450.
Balancing screws set No. 309906 size 180.

Technical description

External \varnothing D	27 mm
Cooling channel bore	lockable
L_2	50.9 mm
$\varnothing D_2$	21 mm
Overhang dimension A	120 mm
Clamping $\varnothing D_1$	6 mm
$\varnothing D_3$	80 mm
Adapter	SK 50 A = 120
Arbor standard	ISO 7388-1
Shape	ADB
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HPC
Vibration	damped
Type of product	Shrink-fit chuck