



## LED rechargeable rod lamp, Length: 300mm



### Order data

Order number	081564 300
GTIN	4067263252573
Item class	02A

### Description

#### Version:

Foldable and slim LED cordless work lamps with **three lighting options**. Can be used in many applications due to the slim design and two magnets.

- **One spotlight and two main lights.**
- **Front main light dimmable in 2 light levels.**
- **Can be folded 180°.**
- **Battery charge is always clearly visible through the LED display.**

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Supplied with USB-C charging cable.

### Technical description

Power supply	Mains operated
Bulb	LED module

Illumination	80 - 300 lm
Type of rechargeable battery	Lithium-ion
IP Index of Protection	IP 54
Working life	3 - 6 h
Number of rechargeable batteries contained	1
Weight	98 g
Overall width	35 mm
Type of product	Inspection lamp