

**Garant**

**HSS boring bar AH.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 8/06mm**


**Order data**

Order number	260022 8/06
GTIN	4067263570561
Item class	21T

**Technical description**

Shank Ø D <sub>s</sub>	8 mm
Centre offset L <sub>3</sub>	5 mm
Minimum pre-drill Ø D <sub>min</sub>	10 mm
Pack of insert screws	269028 7
Setting angle κ	95 degrees
Overall length L	125 mm
Overhang L <sub>1</sub>	40 mm
Clamping height L <sub>2</sub>	7 mm
Insert size	6 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	AH08K SCLCR/L06
Standard	DIN 8024
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8