

Garant

HSS boring bar AH.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 8/06mm


Order data

Order number	260023 8/06
GTIN	4067263103288
Item class	21T

Technical description

ISO code toolholder	AH08K SCLCR/L06
Overall length L	125 mm
Clamping height L ₂	7 mm
Shank Ø D _s	8 mm
Pack of insert screws	269028 7
Insert size	6 mm
Setting angle κ	95 degrees
Centre offset L ₃	5 mm
Minimum pre-drill Ø D _{min}	10 mm
suitable indexable insert	CC.. 0602..
Overhang L ₁	40 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8