

**Garant**
**GARANT Master Mute boring bar, left-hand, Shank  $\varnothing$  / insert size: 12/06mm**

**Order data**

Order number	260045 12/06
GTIN	4067263623373
Item class	29E

**Description**
**Version:**

Round shank without clamping face.

**Note:**

Do not clamp on the area marked S!

**Technical description**

Insert size	6 mm
Centre offset $L_3$	8.5 mm
Pack of insert screws	269028 38
Shank $\varnothing D_s$	12 mm
Series	Master Mute
ISO code toolholder	A12X SCLCR/L06
Setting angle $\kappa$	95 degrees
Minimum pre-drill $\varnothing D_{min}$	16 mm
Overhang $L_1$	60 mm
suitable indexable insert	CC.. 0602..
Overall length L	120 mm
non-clamping range S	72 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar