

**Garant**
**Clamping toolholder SCLCR 95°, for indexable inserts SC., right-hand, Shank / insert size: 16/09mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 260026 16/09  |
| GTIN         | 4067263122371 |
| Item class   | 21U           |

**Description**
**Version:**

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco toolholders No. 319006 – 311936 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

|                                 |                 |
|---------------------------------|-----------------|
| Insert size                     | 9 mm            |
| Head length L <sub>1</sub>      | 30 mm           |
| Overall length L                | 80 mm           |
| suitable indexable insert       | CC.. 09T3..     |
| Functional width L <sub>4</sub> | 20 mm           |
| Series                          | Master Eco      |
| ISO code toolholder             | SCLCR/L 1616F09 |
| Pack of insert screws           | 269028 28       |
| Shank size                      | 16 mm           |
| Standard                        | DIN ISO 5610    |

|                        |                               |
|------------------------|-------------------------------|
| Application type       | right-hand                    |
| Through-coolant        | yes                           |
| Setting angle $\kappa$ | 95 degrees                    |
| Application            | External longitudinal turning |
| Application            | External longitudinal turning |
| Type of product        | Screw-on toolholder           |