

Garant
for indexable inserts SD.. SDJC 93°, left-hand, Shank / insert size: 16/11mm

Order data

Order number	260293 16/11
GTIN	4067263122500
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holder No. 319006 – 311936 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Shim	269007 1
Insert size	11 mm
Head length L ₁	30 mm
Functional width L ₄	20 mm
Series	Master Eco
ISO code toolholder	SDJCR/L 1616H11
Shank size	16 mm
suitable indexable insert	DC.. 11T3..
Shim screw	269013 6
Pack of insert screws	269023 3
Overall length L	100 mm

Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder