

Garant**Eco clamping toolholder SVJB 93°, for indexable inserts SV.., right-hand,
Shank / insert size: 20/11 mm****Order data**

Order number	261122 20/11
GTIN	4067263122531
Item class	21U

Description**Version:**

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Series	Master Eco
suitable indexable insert	VB.. 1103..
Functional width L ₄	25 mm
ISO code toolholder	SVJBR/L 2020X11
Head length L ₁	35 mm
Insert size	11 mm
Pack of insert screws	269023 1
Overall length L	95 mm
Shank size	20 mm
Standard	Works standard

Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder