

Garant
**Eco clamping toolholder SVJB 93°, for indexable inserts SV.., left-hand,
Shank / insert size: 20/16mm**

Order data

Order number	261123 20/16
GTIN	4067263122579
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

ISO code toolholder	SVJBR/L 2020H16
suitable indexable insert	VB.. 1604..
Overall length L	100 mm
Series	Master Eco
Insert size	16 mm
Shim	259033 5
Head length L ₁	40 mm
Pack of insert screws	269023 3
Shank size	20 mm
Shim screw	269013 7

Functional width L ₄	25 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder