

**Garant**

**Eco clamping toolholder SVJC 93°, for indexable inserts SV.., right-hand,  
Shank / insert size: 20/11 mm**



## Order data

|              |               |
|--------------|---------------|
| Order number | 261136 20/11  |
| GTIN         | 4067263122609 |
| Item class   | 21U           |

## Description

### Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

### Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

## Technical description

|                                 |                 |
|---------------------------------|-----------------|
| Series                          | Master Eco      |
| Overall length L                | 95 mm           |
| Pack of insert screws           | 269023 1        |
| Shank size                      | 20 mm           |
| Insert size                     | 11 mm           |
| ISO code toolholder             | SVJCR/L 2020X11 |
| Head length L <sub>1</sub>      | 35 mm           |
| Functional width L <sub>4</sub> | 25 mm           |
| suitable indexable insert       | VC.. 1103..     |
| Standard                        | Works standard  |

|                        |                               |
|------------------------|-------------------------------|
| Application type       | right-hand                    |
| Through-coolant        | yes                           |
| Setting angle $\kappa$ | 93 degrees                    |
| Application            | External longitudinal turning |
| Application            | External longitudinal turning |
| Type of product        | Screw-on toolholder           |