

Garant**GARANT Master Eco VDI toolholder, Form B3 radial right-hand, short, Shank
Ø d1: 50mm****Order data**

Order number	319026 50
GTIN	4067263237594
Item class	31V

Description**Version:**

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

b ₁	100 mm
Colour code for VDI shanks	VDI 50
Shank Ø D ₁	50 mm
l ₂	55 mm
h ₅	35 mm
l ₁	30 mm

h_1	25 mm
h_6	60 mm
b_2	50 mm
Shape	B
Type of product	VDI tool arbor