

Garant

**GARANT Master Eco VDI toolholder, Form B3 radial right-hand, short, Shank
Ø d1: 40mm**



Order data

Order number	319026 40
GTIN	4067263237587
Item class	31V

Description

Version:

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

b ₂	42.5 mm
Colour code for VDI shanks	VDI 40
h ₆	48 mm
h ₁	25 mm
h ₅	42.5 mm
b ₁	85 mm

l_2	44 mm
Shank $\varnothing D_1$	40 mm
l_1	22 mm
Shape	B
Type of product	VDI tool arbor