

Garant**GARANT Master Eco VDI toolholder, Form B3 radial right-hand, short, Shank
Ø d1: 25mm****Order data**

Order number	319026 25
GTIN	4067263237563
Item class	31V

Description**Version:**

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

b ₂	30 mm
b ₁	55 mm
h ₆	30 mm
h ₅	27 mm
Shank Ø D ₁	25 mm
h ₁	16 mm

l_1	16 mm
l_2	30 mm
Colour code for VDI shanks	VDI 25
Shape	B
Type of product	VDI tool arbor