

Garant**GARANT Master Eco VDI toolholder, Form B3 radial right-hand, short, Shank
Ø d1: 30mm****Order data**

Order number	319026 30
GTIN	4067263237570
Item class	31V

Description**Version:**

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Shank Ø D ₁	30 mm
l ₂	40 mm
b ₂	35 mm
h ₅	35 mm
Colour code for VDI shanks	VDI 30
l ₁	22 mm

b_1	70 mm
h_6	38 mm
h_1	20 mm
Shape	B
Type of product	VDI tool arbor