

**Garant**

**GARANT Master Eco VDI toolholder, Form B1 radial right-hand, short, Shank  
Ø d1: 50mm**



## Order data

Order number	319006 50
GTIN	4067263201793
Item class	31V

## Description

### Version:

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

### Application:

Mainly for external machining.

### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

## Technical description

Colour code for VDI shanks	VDI 50
b <sub>2</sub>	50 mm
h <sub>5</sub>	35 mm
Shank Ø D <sub>1</sub>	50 mm
b <sub>1</sub>	100 mm
l <sub>2</sub>	55 mm

$h_1$	25 mm
$l_1$	30 mm
$h_6$	60 mm
Shape	B
Type of product	VDI tool arbor