



Toolholder form C4 axial, left-hand, Shank \varnothing d1: 50mm



Order data

| | |
|--------------|---------------|
| Order number | 319137 50 |
| GTIN | 4067263237648 |
| Item class | 32V |

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

| | |
|------------------------------------|--------|
| h_5 | 50 mm |
| Shank \varnothing D ₁ | 50 mm |
| b_1 | 100 mm |
| h_1 | 32 mm |
| b_2 | 50 mm |
| h_2 | 34 mm |
| l_1 | 100 mm |

| | |
|----------------------------|----------------|
| h ₆ | 60 mm |
| Shank width b ₃ | 30 mm |
| Colour code for VDI shanks | VDI 50 |
| Shape | C |
| Type of product | VDI tool arbor |