

**Toolholder form B4 radial left-hand, short, Shank \varnothing d1: 20mm****Order data**

Order number	319037 20
GTIN	4067263015369
Item class	32V

Description**Version:**

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

h_5	25 mm
b_2	30 mm
h_2	22 mm
l_1	16 mm
h_6	30 mm

l_2	30 mm
h_1	16 mm
b_1	55 mm
Colour code for VDI shanks	VDI 20
Shank $\varnothing D_1$	20 mm
Shape	B
Type of product	VDI tool arbor