

**Garant**
**GARANT Master Eco VDI toolholder, Form B5 radial right-hand, long, Shank  $\varnothing$  d1: 40mm**


## Order data

Order number	319046 40
GTIN	4067263237761
Item class	31V

## Description

### Version:

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**GARANT Eco** – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

### Application:

Mainly for external machining.

### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

## Technical description

Colour code for VDI shanks	VDI 40
$l_2$	44 mm
$h_1$	25 mm

$b_2$	75.5 mm
$h_6$	48 mm
Shank $\varnothing D_1$	40 mm
$l_1$	22 mm
$h_5$	38.5 mm
$b_1$	118 mm
Shape	B
Type of product	VDI tool arbor