

Garant

GARANT Master Eco VDI toolholder, Form B6 radial left-hand, long, Shank Ø d1: 40mm



Order data

Order number	319056 40
GTIN	4067263237785
Item class	31V

Description

Version:

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Colour code for VDI shanks	VDI 40
b ₂	75.5 mm
b ₁	118 mm

Shank $\varnothing D_1$	40 mm
l_1	22 mm
h_6	48 mm
l_2	44 mm
h_5	38.5 mm
h_1	25 mm
Shape	B
Type of product	VDI tool arbor