

Garant**GARANT Master Eco VDI toolholder, Form C1 axial, right hand, Shank Ø d1: 40mm****Order data**

Order number	319106 40
GTIN	4067263237969
Item class	31V

Description**Version:**

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

h_5	32.5 mm
l_1	85 mm
b_2	42.5 mm
b_1	85 mm

Shank Ø D ₁	40 mm
Colour code for VDI shanks	VDI 40
h ₁	25 mm
h ₆	48 mm
h ₂	34 mm
Shank width b ₃	20.5 mm
Shape	C
Type of product	VDI tool arbor