

**Garant**

**GARANT Master Eco VDI toolholder, Form C1 axial, right hand, Shank  $\varnothing$  d1: 50mm**



## Order data

Order number	319106 50
GTIN	4067263237976
Item class	31V

## Description

### Version:

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**GARANT Eco** – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

### Application:

For face cutting in.

### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

## Technical description

$h_2$	41 mm
$l_1$	100 mm
$h_5$	50 mm
$b_1$	100 mm

$h_1$	25 mm
$b_2$	50 mm
Shank width $b_3$	26 mm
$h_6$	60 mm
Colour code for VDI shanks	VDI 50
Shank $\varnothing D_1$	50 mm
Shape	C
Type of product	VDI tool arbor