

**Garant**

**GARANT Master Eco VDI toolholder, Form B6 radial left-hand, long, Shank Ø d1: 30mm**



## Order data

Order number	319056 30
GTIN	4067263237778
Item class	31V

## Description

### Version:

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

**GARANT Eco** – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

### Application:

Mainly for external machining.

### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

## Technical description

b <sub>2</sub>	65 mm
h <sub>1</sub>	20 mm
l <sub>1</sub>	22 mm

Colour code for VDI shanks	VDI 30
Shank $\varnothing D_1$	30 mm
$h_5$	36 mm
$l_2$	40 mm
$h_6$	38 mm
$b_1$	100 mm
Shape	B
Type of product	VDI tool arbor