

Garant

GARANT Master Eco VDI toolholder, Form C1 axial, right hand, Shank \varnothing d1: 20mm



Order data

Order number	319106 20
GTIN	4067263237938
Item class	31V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

h_6	30 mm
b_1	52 mm
h_1	16 mm
h_5	25 mm

Colour code for VDI shanks	VDI 20
b_2	27 mm
h_2	22 mm
Shank width b_3	13 mm
l_1	55 mm
Shank $\varnothing D_1$	20 mm
Shape	C
Type of product	VDI tool arbor