

**Garant**
**GARANT Master Eco VDI toolholder, Form B7 radial right-hand, long, Shank  $\varnothing$  d1: 40mm**

**Order data**

Order number	319066 40
GTIN	4067263237907
Item class	31V

**Description**
**Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**Application:**

Mainly for external machining.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

$l_2$	44 mm
$l_1$	22 mm
Colour code for VDI shanks	VDI 40
$h_5$	42.5 mm
$h_6$	48 mm
$b_2$	75.5 mm

h <sub>1</sub>	25 mm
b <sub>1</sub>	118 mm
Shank Ø D <sub>1</sub>	40 mm
Shape	B
Type of product	VDI tool arbor