

Garant
GARANT Master Eco VDI toolholder, Form C3 axial, right hand, Shank \varnothing d1: 20mm

Order data

| | |
|--------------|---------------|
| Order number | 319126 20 |
| GTIN | 4067263238034 |
| Item class | 31V |

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

| | |
|-------|-------|
| h_6 | 30 mm |
| b_1 | 52 mm |
| l_1 | 55 mm |
| h_5 | 25 mm |

| | |
|----------------------------|----------------|
| Shank width b_3 | 13 mm |
| h_2 | 22 mm |
| h_1 | 16 mm |
| Shank $\varnothing D_1$ | 20 mm |
| Colour code for VDI shanks | VDI 20 |
| b_2 | 27 mm |
| Shape | C |
| Type of product | VDI tool arbor |