

Garant**GARANT Master Eco VDI toolholder, Form C2 axial, left-hand, Shank Ø d1: 50mm****Order data**

Order number	319116 50
GTIN	4067263238027
Item class	31V

Description**Version:**

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

b ₂	50 mm
h ₅	50 mm
h ₂	41 mm
Shank Ø D ₁	50 mm

l_1	100 mm
b_1	100 mm
h_1	25 mm
Shank width b_3	26 mm
Colour code for VDI shanks	VDI 50
h_6	60 mm
Shape	C
Type of product	VDI tool arbor