

Garant
GARANT Master Eco VDI toolholder, Form C4 axial, left-hand, Shank \varnothing d1: 40mm

Order data

| | |
|--------------|---------------|
| Order number | 319136 40 |
| GTIN | 4067263238119 |
| Item class | 31V |

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, GARANT Eco – system grooving toolholders No. 273830 – 273891 and GARANT Eco – parting-off toolholder No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

| | |
|------------------------------------|---------|
| Shank \varnothing D ₁ | 40 mm |
| b ₂ | 42.5 mm |
| h ₆ | 48 mm |
| b ₁ | 85 mm |

| | |
|----------------------------|----------------|
| Shank width b_3 | 20.5 mm |
| h_5 | 32.5 mm |
| Colour code for VDI shanks | VDI 40 |
| h_1 | 25 mm |
| h_2 | 34 mm |
| l_1 | 85 mm |
| Shape | C |
| Type of product | VDI tool arbor |