

Garant
GARANT Master Eco VDI toolholder, Form C4 axial, left-hand, Shank \varnothing d1: 30mm

Order data

Order number	319136 30
GTIN	4067263238102
Item class	31V

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, GARANT Eco – system grooving toolholders No. 273830 – 273891 and GARANT Eco – parting-off toolholder No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Shank width b_3	17 mm
h_2	29 mm
b_2	35 mm
h_1	20 mm

l_1	70 mm
h_5	28 mm
h_6	38 mm
b_1	70 mm
Shank $\varnothing D_1$	30 mm
Colour code for VDI shanks	VDI 30
Shape	C
Type of product	VDI tool arbor