

Garant

Water pump pliers with stepped fine adjustment, black, overall length: 300mm

**Order data**

Order number	706001 300
GTIN	4067263031468
Item class	71B

Description**Version:**

Box joint designed to prevent fingers being trapped. Push-button **fine step adjustment**, which also allows for quick adjustments directly on the workpiece. Concave profile serrated jaws, self-clamping. The teeth also run against each other in the rear of the jaw for a tight grip. Surface manganese phosphated, polished teeth. Ergonomically shaped handles with non-slip plastic coating.

Standard:

DIN ISO 8976

Material:

Chrome vanadium steel, drop forged.

Technical description

Jaw capacity for pipes	2.3/4 in
Hexagon across flats	60 mm
overall length	300 mm
Number of fine adjustment steps	30
Surface	manganese phosphated, polished jaws
Standard	DIN ISO 8976
Type of jaws	concave profile serrated jaws

Material	Chromium vanadium steel
non-sparking	no
Quick adjustment	yes
Stepped fine adjustment	yes
Self-locking	yes
Protection against trapping fingers	yes
Type of product	Pipe wrench and water pump pliers