

## Wheel brush with shank Stainless steel wire 0.20 mm, Brush $\varnothing D_1 \times$ bristle width $L_1$ : 30X6mm



### Order data

Order number	574253 30X6
GTIN	4067263934745
Item class	57H

### Description

#### Version:

Waved special high quality wire, **shank  $\varnothing$  6 mm.**

#### Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

### Technical description

Brush $\varnothing D_1$	30 mm
Bristle thickness	0.2 mm
Bristle width $L_1$	6 mm
maximum speed	20000 min <sup>-1</sup>
Length of brush section $H_1$	6 mm
Shank $\varnothing D_s$	6 mm

Brush material	Stainless steel wire
Twisted knotting	waved
Type of product	Wheel brush