

**Garant****Universal tool set XXL 70 pieces, Number of pieces: 70****Order data**

Order number	685502 70
GTIN	4067263309154
Item class	66H

**Description****Version:**

Modular plastic L-BOXX® case of shock and impact-resistant ABS plastic, fully splash-proof. The sturdy click-on mechanism allows the case to be quickly and easily attached and detached, and also the transport together of several modular plastic cases up to 40 kg. Lid can be loaded to 100 kg, loading capacity up to 25 kg.

**Function:**

IPX4: Protected against splashed water from all directions, but without any protection against foreign bodies or touching.

**Supplied with:**

Sockets bi-hexagon: 1 pc. each No. 642129 size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32; 34

Screwdriver bits hexagon: 1 pc. each No. 643229 size 4; 5; 6; 7; 8; 10; 12; 14

T-handle: 1 pc. No. 641329 size 295

Extension: 1 pc. each No. 641029 size 75; 125; 250

Universal joint: 1 pc. No. 641629 size 1/2

Ratchet: 1 pc. No. 640025 size 1/2

Locking tape measure: 1 pc. No. 462201 size 2.5

Combination spanner: 1 pc. each No. 613600 size 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24

Combination pliers: 1 pc. No. 700940 size 160  
 Snipe nose pliers: 1 pc. No. 713040 size 200  
 Diagonal side cutter: 1 pc. No. 724840 size 160  
 Slot-head screwdriver: 1 pc. each No. 660032 size 2; 3.5; 5.5; 6.5  
 Screwdriver for Phillips: 1 pc. each No. 667702 size 1; 2  
 Hexagon key L-wrench set with ball point: 1 pc. No. 627132 size 9  
 Cutters: 1 pc. No. 845020  
 Lid inlay: 1 pc. No. 693352  
 Stored in: L-BOXX® No. 693330 size 238

**Note:**

**Supplied with tools sorted in L-BOXX®.**

## Technical description

Weight	11 kg
IP Index of Protection	IP X4
Number of pieces	70
Square drive	1/2 in
Type of product	Tool set

## Accessories

Tape measure with viewing window Band length 2,5 m	462201 2,5
Combination spanner Width across flats 15 mm	613500 15
Combination spanner Width across flats 16 mm	613500 16
Combination spanner Width across flats 10 mm	613600 10
Combination spanner Width across flats 11 mm	613600 11
Combination spanner Width across flats 12 mm	613600 12
Combination spanner Width across flats 13 mm	613600 13
Combination spanner Width across flats 14 mm	613600 14
Combination spanner Width across flats 15 mm	613600 15
Combination spanner Width across flats 16 mm	613600 16
Combination spanner Width across flats 17 mm	613600 17

Combination spanner Width across flats 18 mm	613600 18
Combination spanner Width across flats 19 mm	613600 19
Combination spanner Width across flats 20 mm	613600 20
Combination spanner Width across flats 21 mm	613600 21
Combination spanner Width across flats 22 mm	613600 22
Combination spanner Width across flats 24 mm	613600 24
Combination spanner Width across flats 5,5 mm	613600 5,5
Combination spanner Width across flats 6 mm	613600 6
Combination spanner Width across flats 7 mm	613600 7
Combination spanner Width across flats 8 mm	613600 8
Combination spanner Width across flats 9 mm	613600 9
Hexagon key L-wrench set, with retainer ballchrome-plated Number of screwdrivers 9	627132 9
Reversible ratchet, 1/2 inch with ejector Type 1/2	640025 1/2
Extension, 1/2 inch overall length 130 mm	641029 130
Extension, 1/2 inch overall length 255 mm	641029 255
Extension, 1/2 inch overall length 75 mm	641029 75
T-handle, 1/2 inch overall length 295 mm	641329 295
Universal joint, 1/2 inch Type 1/2	641629 1/2
Bi-hexagon socket, 1/2 inch Width across flats 10 mm	642129 10
Bi-hexagon socket, 1/2 inch Width across flats 11 mm	642129 11
Bi-hexagon socket, 1/2 inch Width across flats 12 mm	642129 12
Bi-hexagon socket, 1/2 inch Width across flats 13 mm	642129 13
Bi-hexagon socket, 1/2 inch Width across flats 14 mm	642129 14
Bi-hexagon socket, 1/2 inch Width across flats 15 mm	642129 15
Bi-hexagon socket, 1/2 inch Width across flats 16 mm	642129 16
Bi-hexagon socket, 1/2 inch Width across flats 17 mm	642129 17
Bi-hexagon socket, 1/2 inch Width across flats 18 mm	642129 18
Bi-hexagon socket, 1/2 inch Width across flats 19 mm	642129 19
Bi-hexagon socket, 1/2 inch Width across flats 21 mm	642129 21

Bi-hexagon socket, 1/2 inch Width across flats 22 mm	642129 22
Bi-hexagon socket, 1/2 inch Width across flats 24 mm	642129 24
Bi-hexagon socket, 1/2 inch Width across flats 27 mm	642129 27
Bi-hexagon socket, 1/2 inch Width across flats 30 mm	642129 30
Bi-hexagon socket, 1/2 inch Width across flats 32 mm	642129 32
Bi-hexagon socket, 1/2 inch Width across flats 34 mm	642129 34
Bi-hexagon socket, 1/2 inch Width across flats 8 mm	642129 8
Hexagon bit socket, 1/2 inch Hexagon 10 mm	643229 10
Hexagon bit socket, 1/2 inch Hexagon 12 mm	643229 12
Hexagon bit socket, 1/2 inch Hexagon 14 mm	643229 14
Hexagon bit socket, 1/2 inch Hexagon 4 mm	643229 4
Hexagon bit socket, 1/2 inch Hexagon 5 mm	643229 5
Hexagon bit socket, 1/2 inch Hexagon 6 mm	643229 6
Hexagon bit socket, 1/2 inch Hexagon 7 mm	643229 7
Hexagon bit socket, 1/2 inch Hexagon 8 mm	643229 8
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 2 mm	660030 2
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 3,5 mm	660030 3,5
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 5,5 mm	660030 5,5
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 6,5 mm	660030 6,5
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 1	667690 1
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 2	667690 2
Modular plastic case L-BOXX®, empty Type 238	693330 238
Lid inlay individual	693352
Combination pliers, chrome-plated, with 2-component grips overall length 160 mm	700940 160
	713040 200

Snipe nose pliers, straight, chrome-plated, with grips  
overall length 200 mm

Side cutter chrome-plated, with grips overall length 160  
mm

724840 160

General-purpose knife with 2-component handle with 3  
blades, 18 mm

845020