

**Garant**
**Clamping toolholder CKJNL 93°, for indexable inserts KNUX., left-hand,  
Shank / insert size: 32/16mm**

**Order data**

Order number	251009 32/16
GTIN	4045197654656
Item class	21T

**Technical description**

Shim pins pack	259044 3
Insert size	16 mm
Head length L <sub>1</sub>	32 mm
Clamp	259038 17
Screw for clamp	259021 3
suitable indexable insert	KNUX 1604.. R/L
Functional width L <sub>4</sub>	40 mm
Spring	259046 3
ISO code toolholder	CKJNR/L 3232P16
Shim	259031 6
Shank size	32 mm
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

Screw for clamping claw Type 3	259021 3
Shim Type 6	259031 6
Clamping claw Type 17	259038 17
Set of shim pins 10 pieces Type 3	259044 3
Spring Type 3	259046 3
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4