

Garant
**Clamping toolholder PWLNR 95°, for indexable inserts WN., right-hand,
Shank / insert size: 25/08mm**

Order data

Order number	251916 25/08
GTIN	4045197651341
Item class	21T

Technical description

Shim pins pack	259044 2
Head length L ₁	21 mm
Lever	259015 2
Shim	259031 40
Lever screw	259018 2
Functional width L ₄	32 mm
ISO code toolholder	PWLNR/L 2525M08
Shank size	25 mm
Insert size	8 mm
suitable indexable insert	WN.. 0804..
Shim punches pack	259047 2
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 2	259015 2
Lever screw Type 2	259018 2
Shim Type 40	259031 40
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3