

Garant
**Clamping toolholder PWLNL 95°, for indexable inserts WN., left-hand,
Shank / insert size: 25/06mm**

Order data

Order number	251917 25/06
GTIN	4045197651372
Item class	21T

Technical description

Shim	259031 25
Lever	259015 9
ISO code toolholder	PWLNR/L 2525M06
Functional width L ₄	32 mm
Shim punches pack	259047 3
suitable indexable insert	WN.. 0604..
Insert size	6 mm
Shank size	25 mm
Head length L ₁	16 mm
Lever screw	259018 6
Shim pins pack	259044 5
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 25	259031 25
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5