

Garant

Steel boring bar A.. PWLNR 95°, for indexable inserts WN., right-hand, Shank Ø / insert size: 20/06mm


Order data

Order number	251942 20/06
GTIN	4045197651488
Item class	21T

Technical description

suitable indexable insert	WN.. 0604..
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Insert size	6 mm
Centre offset L_3	13 mm
Lever	259015 14
Lever screw	259018 10
ISO code toolholder	A20Q PWLNR/L06
Overall length L	180 mm
Clamping height L_2	19 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Lever Type 14	259015 14
Lever screw Type 10	259018 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2