

Garant

Steel boring bar A.. MWLNL 95°, for indexable inserts WN.., left-hand, Shank Ø / insert size: 25/08mm


Order data

Order number	251937 25/08
GTIN	4045197651440
Item class	21T

Technical description

Pin	259049 3
Minimum pre-drill Ø D _{min}	32 mm
Shim	259031 41
Insert size	8 mm
suitable indexable insert	WN.. 0804..
ISO code toolholder	A25R MWLNR/L08
Clamping claw	259038 12
Screw set	259023 3
Centre offset L ₃	17 mm
Overall length L	200 mm
Clamping height L ₂	24 mm
Setting angle κ	95 degrees
Shank Ø D _s	25 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of screws 10 pieces Type 3	259023 3
Shim Type 41	259031 41
Clamping claw Type 12	259038 12
Pin Type 3	259049 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15