

Garant

**Clamping toolholder PWLNR 95°, for indexable inserts WN., right-hand,
Shank / insert size: 16/06mm**



Order data

Order number	251916 16/06
GTIN	4045197651297
Item class	21T

Technical description

suitable indexable insert	WN.. 0604..
Shank size	16 mm
Shim punches pack	259047 3
ISO code toolholder	PWLNR/L 1616H06
Head length L ₁	16 mm
Functional width L ₄	20 mm
Shim pins pack	259044 5
Lever	259015 9
Lever screw	259018 6
Insert size	6 mm
Shim	259031 25
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 25	259031 25
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5