

Garant

**Steel boring bar A.. MWLNL 95°, for indexable inserts WN.., left-hand, Shank
Ø / insert size: 32/08mm**


Order data

Order number	251937 32/08
GTIN	4045197651457
Item class	21T

Technical description

suitable indexable insert	WN.. 0804..
Minimum pre-drill Ø D _{min}	40 mm
Insert size	8 mm
Screw set	259023 3
Clamping claw	259038 12
Centre offset L ₃	22 mm
Pin	259049 5
Shim	259031 41
ISO code toolholder	A32S MWLNR/L08
Overall length L	250 mm
Clamping height L ₂	31 mm
Setting angle κ	95 degrees
Shank Ø D _s	32 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of screws 10 pieces Type 3	259023 3
Shim Type 41	259031 41
Clamping claw Type 12	259038 12
Pin Type 5	259049 5
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15