

Garant

Steel boring bar A.. PWLNR 95°, for indexable inserts WN., right-hand, Shank Ø / insert size: 16/06mm


Order data

Order number	251942 16/06
GTIN	4045197651471
Item class	21T

Technical description

Insert size	6 mm
Minimum pre-drill Ø D _{min}	21 mm
Lever	259015 14
suitable indexable insert	WN.. 0604..
ISO code toolholder	A16M PWLNR/L06
Centre offset L ₃	11 mm
Lever screw	259018 10
Overall length L	150 mm
Clamping height L ₂	15.25 mm
Setting angle κ	95 degrees
Shank Ø D _s	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Lever Type 14	259015 14
Lever screw Type 10	259018 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2