

**Garant**

**Steel boring bar A.. PWLNL 95°, for indexable inserts WN., left-hand, Shank  
Ø / insert size: 20/06mm**


**Order data**

Order number	251943 20/06
GTIN	4045197651501
Item class	21T

**Technical description**

Centre offset $L_3$	13 mm
Lever	259015 14
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Lever screw	259018 10
Insert size	6 mm
suitable indexable insert	WN.. 0604..
ISO code toolholder	A20Q PWLNR/L06
Overall length L	180 mm
Clamping height $L_2$	19 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

---

## Accessories

Lever Type 14	259015 14
Lever screw Type 10	259018 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2