

**Garant**
**Clamping toolholder PSKNR 75°, for indexable inserts SN., right-hand,  
Shank / insert size: 32/15mm**

**Order data**

Order number	251110 32/15
GTIN	4045197656735
Item class	21T

**Technical description**

Shim punches pack	259047 4
Functional width L <sub>4</sub>	40 mm
Shim pins pack	259044 6
Head length L <sub>1</sub>	30 mm
Shank size	32 mm
ISO code toolholder	PSKNR/L 3232P15
Insert size	15 mm
suitable indexable insert	SN.. 1506..
Shim	259031 37
Lever screw	259018 11
Lever	259015 12
Overall length L	170 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 37	259031 37
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15