

Garant

**Clamping toolholder SDHCL 107,5°, for indexable inserts DC., left-hand,
Shank / insert size: 10/07mm**



Order data

Order number	260307 10/07
GTIN	4045197654885
Item class	21T

Technical description

Pack of insert screws	269028 22
suitable indexable insert	DC.. 0702..
Shank size	10 mm
Functional width L ₄	12 mm
Head length L ₁	7 mm
Insert size	7 mm
ISO code toolholder	SDHCR/L 1010E07
Overall length L	70 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15