

Garant
**Clamping toolholder PSSNR 45°, for indexable inserts SN., right-hand,
Shank / insert size: 32/15mm**

Order data

Order number	251112 32/15
GTIN	4045197656780
Item class	21T

Technical description

ISO code toolholder	PSSNR/L 3232P15
Shim punches pack	259047 4
Insert size	15 mm
Shim	259031 37
Lever screw	259018 11
Shim pins pack	259044 6
Head length L ₁	36 mm
Lever	259015 12
suitable indexable insert	SN.. 1506..
Shank size	32 mm
Functional width L ₄	40 mm
Overall length L	170 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 37	259031 37
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15